

Aicube -- Care with Love



Guangzhou SELAQUA Sanitary Ware Co., Ltd
Jintian Industrial Park, Huadong Town, Huadu
District, Guangzhou City, Guangdong Province, China.

Contact: Katie Peng
Sales Manager
M: +86 18620266308
E: katie@aicubecare.com

PRODUCT DETAILS

Type	Height adjustable U-shaped Grab Bar
Item Code	XHB-U658
Range	Bathroom Accessories
Materials	1. The U shaped grab bar and wall track system are constructed with super solid aluminum. 2. The fixing kits and fasteners are made of stainless steel. 3. The front cover of the vertical wall track is PVC.
Finish	Bright Chrome or Black

Technical Details and Descriptions:

Ergonomic Design-The bathroom grab bar adopts ergonomic design, which accords with the grip feeling of the people. The smooth surface and curved design make it comfortable to hold and never hurt your hands.

Saving Space -The folding grab bar, with 90° vertical flip-up design, help you save precious space when the bar is not in use. The safety bar has a long life service.

Height Adjustable- The height adjustable grab arm is attach on the vertical wall track. The height is adjustable by loosening the side lock mechanism by hand without any tools.

Install Easily - This toilet grab bar with completed accessories to ensure long-lasting service life and stability, easily attaches the vertical wall track to the wall. You can make this grab handles be your bathroom helper in a short time.

Standard and Warranty

Standard	ISO17966:2016
Warranty	We makes a commitment to remedy material and manufacturing defects for a period of 3 years from the invoicing date.

Cleanning and Care Guide


1. The product is to be cleaned with hot water or a mild soapy cleaning agent.
2. We recommend that chalky deposits be removed from aluminum parts using a solution of 3:7 acetic acid: tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth, wrung out in clear water. The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.

Warm Note: Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.

IMAGE



TECHNICAL DRAWINGS



Full set with 1 carton box: 77.5x25.5x22.5cm 6kgs